
## υροποι

## TruFLOW Jr. assemblies with balancing and isolation valves

| Job name:                      | Location:       |
|--------------------------------|-----------------|
| Engineer:                      | Date submitted: |
| Contractor:                    | Submitted by:   |
| Manufacturer's representative: | Approved by:    |
|                                |                 |

| Technical data                    |                                     |
|-----------------------------------|-------------------------------------|
| Material                          | Brass                               |
| Manifold size                     | 1 inch                              |
| Loop Cv                           | 1.9 Cv                              |
| End type 1                        | ISO 228-G 1-1/4"                    |
| End type 2                        | ISO 228-G 3/4"                      |
| Temp/pressure ratings             | 73 °F (23 °C) at 160 psi (11 bar)   |
|                                   | 180 °F (82 °C) at 100 psi (6.9 bar) |
|                                   | 200 °F (93 °C) at 80 psi (5.5 bar)  |
| Max. fluid flow rate              | 14 gpm                              |
| Prop 65 label required?           | Yes                                 |
| Product information and applicati |                                     |





The TruFLOW™Jr. Assembly with Balancing and IsolationValves comes fully assembled and ready for installation. Use the TruFLOW Balancing Hex Key on the internal balancing valves of the supply manifold to balance the loops across the manifold. The TruFLOW Jr. Manifold with Isolation Valves allows quick isolation of the loop by turning the black cap on the top of the manifold. For multiple zoning on the manifold, remove the black caps and replace with Uponor Thermal Actuators or Motorized Valve Actuators (MVAs). The manifold assembly is shipped with the appropriate number of TruFLOW Manifold Actuator Adapters. The manifold body ends have R32 unions and the loop outlets have R20 male threads.

| Part name                         | Part<br>no. | A<br>[inch] | B<br>[inch] | C<br>[inch] | D<br>[inch] | E<br>[inch] | F<br>[inch] | G<br>[inch] | H<br>[inch] | Weight<br>per UOM<br>[lbs/UOM] |
|-----------------------------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|--------------------------------|
| TruFLOW Jr. Assembly, B&I, 2-loop | A2660201    | 7.185       | 12.214      | 2.9         | 1.969       | 1.989       | 1.285       | 2.013       | 1.85        | 5.78                           |
| TruFLOW Jr. Assembly, B&I, 3-loop | A2660301    | 9.154       | 12.214      | 2.9         | 1.969       | 1.989       | 1.285       | 2.013       | 1.969       | 7.86                           |
| TruFLOW Jr. Assembly, B&I, 4-loop | A2660401    | 11.122      | 12.214      | 2.9         | 1.969       | 1.988       | 1.285       | 2.013       | 3.937       | 9.95                           |
| TruFLOW Jr. Assembly, B&I, 5-loop | A2660501    | 13.091      | 12.214      | 2.9         | 1.969       | 1.989       | 1.285       | 2.013       | 5.906       | 12.67                          |
| TruFLOW Jr. Assembly, B&I, 6-loop | A2660601    | 15.059      | 12.215      | 2.9         | 1.969       | 1.989       | 1.285       | 2.013       | 7.874       | 14.76                          |
| TruFLOW Jr. Assembly, B&I, 7-loop | A2660701    | 17.028      | 12.214      | 2.9         | 1.969       | 1.989       | 1.285       | 2.013       | 9.843       | 16.84                          |
| TruFLOW Jr. Assembly, B&I, 8-loop | A2660801    | 18.996      | 12.214      | 2.9         | 1.969       | 1.989       | 1.285       | 2.013       | 11.811      | 18.93                          |

| Part name                      | Part no. | Codes                     | Standards                       | Listings     |
|--------------------------------|----------|---------------------------|---------------------------------|--------------|
| TruFLOW Jr. assemblies with    | A II     | IMC IRC NBC of Canada UMC | CSA B137.5 R32: ISO 228-G       | cNSFus-rfh   |
| balancing and isolation valves | All      |                           | 1¼" ASTM F877 R20: ISO 228-G ¾" | civorus-iiii |

| Installation  | Related applications                |
|---|-------------------------------------|
| TruFLOW Jr. Manifolds are fully assembled ready for installation. Use the TruFLOW Balancing Hex   | Radiant Heating and Cooling Systems |
| Key on the internal balancing valves of the supply manifold. The manifold is shipped with the<br>appropriate number of actuator adapters (A2630028). Refer to the Uponor TruFLOW Jr. Manifold | Permafrost Prevention Systems       |
| Instruction Sheet for further information.  | Turf Conditioning Systems           |

## Notes

Manifold body threaded connections:

R32

Manifold loop threaded connections: R20

| Footnotes | Contact information    |                         |  |
|-----------|------------------------|-------------------------|--|
|           | Uponor Inc.            | Uponor Ltd.             |  |
|           | 5925 148th Street West | 6510 Kennedy Road       |  |
|           | Apple Valley, MN 55124 | Mississauga, ON L5T 2X4 |  |
|           | T 800.321.4739         | T 888.594.7726          |  |
|           | F 952.891.2008         | F 800.638.9517          |  |