


TruFLOW Jr. return manifolds with isolation valves

Project information

Job name:	Location:
Engineer:	Date submitted:
Contractor:	Submitted by:
Manufacturer's representative:	Approved by:

Product information and application use

Use the TruFLOW™ Jr. Manifold with Isolation Valves with either the TruFLOW Jr. Manifold with Balancing Valves or the TruFLOW Jr. Valveless Manifold to complete the manifold set. The TruFLOW Jr. Manifold with Isolation Valves allows quick isolation of the loop by turning the black cap on the top of the manifold. For multiple zoning on the manifold, remove the black caps and replace with Uponor Thermal Actuators or Motorized Valve Actuators (MVAs). TruFLOW Manifold Actuator Adapters are included for mounting Thermal Actuators or MVAs. Manifolds are available in 2-, 3- and 4-loop configurations. The manifold body ends have R32 unions and the loop outlets have R20 male threads.



Installation

Manifold is shipped with the appropriate number of actuator adapters (A2630028). Refer to the TruFLOW Jr. Manifold Instruction Sheet or the Uponor Complete Design Assistance Manual for additional information.

Related applications

Radiant Heating and Cooling Systems
Permafrost Prevention Systems
Turf Conditioning Systems

Footnotes

Contact information

Uponor Inc.
5925 148th Street West
Apple Valley, MN 55124
T 800.321.4739
F 952.891.2008

Uponor Ltd.
6510 Kennedy Road
Mississauga, ON L5T 2X4
T 888.594.7726
F 800.638.9517