

# Replacement and spare parts

## Project Information

Job name :	Location :
Engineer :	Date submitted:
Contractor :	Submitted by:
Manufacturer's representative :	Approved by :

## Technical data

Material	Brass
End type 2	BSPP 3/4"
Temp/pressure ratings	73 °F (23 °C) at 160 psi (11 bar) 180 °F (82 °C) at 100 psi (6.9 bar) 200 °F (93 °C) at 80 psi (5.5 bar)
Max. fluid flow rate	21 gpm
Prop 65 label required?	Yes

## Product information and application use

N/A



Part name	Part no.	A [Inch]	B [Inch]	C [Inch]	Weight per UOM [lbs/UOM]	Manifold Body Size (I.D.) [Inch]	End Type 1
Replacement Nut and Bolt Kit for 2" WIPEX	5550220	-	-	-	0.11	-	-
Replacement Gasket for R32 Union Connections	A2620005	-	-	-	0	-	-
Replacement O-ring for 1 1/4" BSP Connections	A2620008	1.527	1.527	0.103	0	-	-
Replacement O-ring for TruFLOW Flow/Temperature Meter	A2620009	0.59	0.59	0.103	0	-	-
TruFLOW Balancing Valve body, replacement part	A2620013	0.991	0.905	0.905	-	-	-
TruFLOW Balancing Valve Plastic Cap, replacement part	A2620014	-	-	-	-	-	-
TruFLOW On/Off Valve Body, replacement part	A2620017	1.439	1.09	1.09	-	-	-
TruFLOW On/Off Valve Plastic Cap, replacement part	A2620018	-	-	-	-	-	-
TruFLOW Manifold Ball-Valve Flat Seat Cone, replacement part	A2620020	-	-	-	-	-	-
TruFLOW Automatic Air Vent with Check Valve, replacement part	A2620050	-	-	-	0.35	-	-
TruFLOW End Cap with Vent and Drain	A2621250	3.156	3.122	1.969	0.61	-	ISO 228-G 1-1/4"
Replacement O-ring for 1" BSP Manifold Connections	A2640004	1.215	1.215	0.103	0	-	-
TruFLOW Jr. Internal Valve Seat Loop Nipple, R20, replacement part	A2640011	-	-	-	-	-	-
TruFLOW Jr. Loop Nipple for valveless manifold, replacement part	A2640018	-	-	-	-	-	-
TruFLOW Jr. Manifold End Cap w/ Vent, 1" BSP	A2641000	-	-	-	0.8	-	ISO 228-G 1"
TruFLOW Jr. Compact Manifold Union, Straight, 1" BSP x R32 Union	A2660032	-	-	-	-	-	-
TruFLOW Jr. Compact Manifold Male Union, Straight 1" BSP x R32 Male	A2661032	-	-	-	-	-	-
EP Heating Manifold Valve Replacement Tool	A2670007	-	-	7.5	0.07	-	-
EP Heating Manifold Replacement O-ring 28.5 x 3mm EPDM	A2670008	-	-	7.5	0	-	-
PEX Foam Stapler Handle, replacement part	E6025001	-	-	-	0.41	-	-
PEX Foam Stapler Jam Door, replacement assembly	E6025002	-	-	-	0.13	-	-
PEX Foam Stapler Spring, replacement part	E6025003	5	0.664	-	0.13	-	-
PEX Foam Stapler Metal Stand, replacement assembly	E6025004	-	-	-	0.48	-	-

PEX Foam Stapler Shear Plate, replacement part	E6025005	4.693	1.5	0.25	0.1	-	-
ProPEX Washing Machine Box Frame	F5830005	10.65	8.5	1	-	-	-
ProPEX Ice Maker Box Frame	F5850005	7.54	5.9	1	-	-	-

Installation	Related applications
N/A	-

Codes	Standards	Listings
-	ASTM F877	-

**Notes**

Connection:  
A2641000: 1" BSP  
A2621250: 1¼" BSP

Footnotes	Contact information		
-	<table border="0"> <tr> <td> <p>Uponor Inc.  5925 148th Street West  Apple Valley, MN 55124  T 800.321.4739  F 952.891.2008</p> </td> <td> <p>Uponor Ltd.  6510 Kennedy Road  Mississauga, ON L5T 2X4  T 888.594.7726  F 800.636.9517</p> </td> </tr> </table>	<p>Uponor Inc.  5925 148th Street West  Apple Valley, MN 55124  T 800.321.4739  F 952.891.2008</p>	<p>Uponor Ltd.  6510 Kennedy Road  Mississauga, ON L5T 2X4  T 888.594.7726  F 800.636.9517</p>
<p>Uponor Inc.  5925 148th Street West  Apple Valley, MN 55124  T 800.321.4739  F 952.891.2008</p>	<p>Uponor Ltd.  6510 Kennedy Road  Mississauga, ON L5T 2X4  T 888.594.7726  F 800.636.9517</p>		