

# **Anillos ProPEX**

Project information	
Job name:	Location:
Engineer:	Fecha de envío:
Contractor:	Presentada por:
Manufacturer's representative:	Approved by:

# Technical data

Material PEX

### Product information and application use

Uponor ProPEX® rings are required to make a proper ProPEX connection. The ProPEX ring with stop includes a leading edge chamfer and stop edge.

Note: Temperature and pressure ratings stated are hydrostatic ratings. For domestic hot-water (DHW) and DHW recirculation installations, operating conditions should not exceed 140°F (60°C) at 80 psi (5.5 bar) in accordance with ASTM F2023. For additional information regarding application-specific temperature and pressure ratings, refer to the Uponor PEX Piping Systems Design and Installation Manual.



Part name	Part no.	A [inch]	B [inch]	C [inch]	Weight per UOM [lbs/UOM]
ProPEX Ring, 3/8	Q4690302	0.732	0.732	0.54	0
ProPEX Ring with Stop, 1/2	Q4690512	0.879	0.879	0.63	0.01
ProPEX Ring with Stop, 5/8	Q4690625	1	1	0.787	0.01
ProPEX Ring with Stop, 3/4	Q4690756	1.128	1.128	0.866	0.01
ProPEX Ring with Stop, 1	Q4691000	1.42	1.42	1.102	0.02
ProPEX Ring with Stop, 1 1/4	Q4691250	1.664	1.664	1.349	0.03
ProPEX Ring with Stop, 1 1/2	Q4691500	1.91	1.91	1.605	0.04
ProPEX Ring with Stop, 2	Q4692000	2.626	2.626	1.968	0.13
ProPEX Ring with Stop, 2 1/2	Q4692500	3.25	3.25	2.605	0.23
ProPEX Ring with Stop, 3	Q4693000	3.865	3.865	3.12	0.4

Part name         Part no.         Codes         Standards         Listings           Anillos ProPEX         All         IMC UPC IBC IRC NBC of Canada IPC UFGS NPC of Canada UMC NSPC         ASTM F1960 ASTM E119/UL S116 ASTM F876 ASTM E84 AULC S116 ASTM F876 AULC S116					
Anillos ProPEX All  All  All  All  All  All  All  Al	Part name	Part no.	Codes	Standards	Listings
ProPEX Ring, 3/8         Q4690302         NSF/ANSI/CAN 61 NSF/ANSI 14         cNSFus-pw           ProPEX Ring with Stop, 1/2         Q4690512         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 5/8         Q4690625         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 3/4         Q4690756         UL 1821 NSF/ANSI/CAN 61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1         Q4691000         UL 1821 NSF-61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1 1/4         Q4691250         UL 1821 NSF-61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 2 1/2         Q4692000         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2 1/2         Q4692500         NSF-61 NSF-14         cNSFus-pw	Anillos ProPEX	All	Canada IPC UFGS NPC of	263 ASTM F876 ASTM E84 ASTM F2023 ASTM E814/ULC S115 ASTM F877 CSA B137.5 ULC S102.2 CSA	4 CSA UL U.P.Code cQAlus
ProPEX Ring with Stop, 1/2         Q4690512         NSF/ANSI/CAN 61 NSF/ANSI 14         cNSFus-pw           ProPEX Ring with Stop, 5/8         Q4690625         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 3/4         Q4690756         UL 1821 NSF/ANSI/CAN 61 NSF/ANSI/CAN 61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1         Q4691000         UL 1821 NSF-61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1 1/4         Q4691250         UL 1821 NSF-61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1 1/2         Q4691500         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2         Q4692000         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2 1/2         Q4692500         NSF-61 NSF-14         cNSFus-pw	In addition, the following parts have	e additional codes, standards, or listings:			
ProPEX Ring with Stop, 5/8         Q4690625         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 3/4         Q4690756         UL 1821 NSF/ANSI/CAN 61 NSF/ANSI/14         cNSFus-pw-fs           ProPEX Ring with Stop, 1         Q4691000         UL 1821 NSF-61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1 1/4         Q4691250         UL 1821 NSF-61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1 1/2         Q4691500         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2         Q4692000         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2 1/2         Q4692500         NSF-61 NSF-14         cNSFus-pw	ProPEX Ring, 3/8	Q4690302		NSF/ANSI/CAN 61 NSF/ANSI 14	cNSFus-pw
ProPEX Ring with Stop, 3/4         Q4690756         UL 1821  NSF/ANSI/CAN 61 NSF/ANSI/CAN 61 NSF/ANSI 14         cNSFus-pw-fs           ProPEX Ring with Stop, 1         Q4691000         UL 1821  NSF-61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1 1/4         Q4691250         UL 1821  NSF-61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1 1/2         Q4691500         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2         Q4692000         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2 1/2         Q4692500         NSF-61 NSF-14         cNSFus-pw	ProPEX Ring with Stop, 1/2	Q4690512		NSF/ANSI/CAN 61 NSF/ANSI 14	cNSFus-pw
ProPEX Ring with Stop, 3/4         Q4690756         61 NSF/ANSI 14         cNSFus-pw-fs           ProPEX Ring with Stop, 1         Q4691000         UL 1821 NSF-61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1 1/4         Q4691250         UL 1821 NSF-61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1 1/2         Q4691500         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2         Q4692000         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2 1/2         Q4692500         NSF-61 NSF-14         cNSFus-pw	ProPEX Ring with Stop, 5/8	Q4690625		NSF-61 NSF-14	cNSFus-pw
ProPEX Ring with Stop, 1 1/4         Q4691250         UL 1821 NSF-61 NSF-14         cNSFus-pw-fs           ProPEX Ring with Stop, 1 1/2         Q4691500         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2         Q4692000         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2 1/2         Q4692500         NSF-61 NSF-14         cNSFus-pw	ProPEX Ring with Stop, 3/4	Q4690756		•	cNSFus-pw-fs
ProPEX Ring with Stop, 1 1/2         Q4691500         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2         Q4692000         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2 1/2         Q4692500         NSF-61 NSF-14         cNSFus-pw	ProPEX Ring with Stop, 1	Q4691000		UL 1821 NSF-61 NSF-14	cNSFus-pw-fs
ProPEX Ring with Stop, 2         Q4692000         NSF-61 NSF-14         cNSFus-pw           ProPEX Ring with Stop, 2 1/2         Q4692500         NSF-61 NSF-14         cNSFus-pw	ProPEX Ring with Stop, 1 1/4	Q4691250		UL 1821 NSF-61 NSF-14	cNSFus-pw-fs
ProPEX Ring with Stop, 2 1/2         Q4692500         NSF-61 NSF-14         cNSFus-pw	ProPEX Ring with Stop, 1 1/2	Q4691500		NSF-61 NSF-14	cNSFus-pw
	ProPEX Ring with Stop, 2	Q4692000		NSF-61 NSF-14	cNSFus-pw
ProPEX Ring with Stop, 3         Q4693000         NSF-61 NSF-14         cNSFus-pw	ProPEX Ring with Stop, 2 1/2	Q4692500		NSF-61 NSF-14	cNSFus-pw
	ProPEX Ring with Stop, 3	Q4693000		NSF-61 NSF-14	cNSFus-pw

#### Installation

Square cut the Uponor PEX tubing. Remove excess material. Slide the ProPEX ring over the end of the tubing (maximum 1 /16" overhang for rings without stop). When using the ProPEX ring with stop, slide the ring on the tubing with the chamfered edge first until the end of the tubing contacts the stop edge. Expand the tubing and ring. If using the ProPEX Manual Expander Tool, rotate the tool a quarter turn after each expansion to prevent the formation of grooves. Remove the expansion tool and fully seat the tubing and ring against the shoulder of the fitting. Make ProPEX connections at temperatures above 5°F/15°C. For more information, refer to the Uponor PEX Piping Systems Design and Installation Guide.

# Related applications

PEX-a Plumbing Systems

AquaSAFE™ Fire Safety Systems

Hydronic Radiant Heating and Cooling Systems

Snow Melting Systems

Turf Conditioning Systems

Permafrost Prevention Systems

### Notes

Degree of crosslinking: 70% to 89%

Footnotes	Contact information		
	Uponor Inc.	Uponor Ltd.	
	5925 148th Street West	6510 Kennedy Road	
•	Apple Valley, MN 55124	Mississauga, ON L5T 2X4	
	T 800.321.4739	T 888.594.7726	
	F 952.891.2008	F 800.638.9517	