Colectores de retorno TruFLOW Jr. con válvulas de


uponor

aislamiento

Project information	
Job name:	Location:
Engineer:	Fecha de envío:
Contractor:	Presentada por:
Manufacturer's representative:	Approved by:

Product information and application use

Use the TruFLOW™ Jr. Manifold with Isolation Valves with either the TruFLOW Jr. Manifold with Balancing Valves or the TruFLOW Jr. Valveless Manifold to complete the manifold set. The TruFLOW Jr. Manifold with Isolation Valves allows quick isolation of the loop by turning the black cap on the top of the manifold. For multiple zoning on the manifold, remove the black caps and replace with Uponor Thermal Actuators or Motorized Valve Actuators (MVAs). TruFLOW Manifold Actuator Adapters are included for mounting Thermal Actuators or MVAs. Manifolds are available in 2-, 3- and 4-loop configurations. The manifold body ends have R32 unions and the loop outlets have R20 male threads.





1	ns	ta	la	io	1 I

Manifold is shipped with the appropriate number of actuator adapters (A2630028). Refer to the TruFLOW Jr. Manifold Instruction Sheet or the Uponor Complete Design Assistance Manual for additional information.

Related applications

Radiant Heating and Cooling Systems

Permafrost Prevention Systems

Turf Conditioning Systems

Contact information		
or Inc. Uponor Ltd.		
Street West 6510 Kennedy Road		
, MN 55124 Mississauga, ON L5T 2X4		
21.4739 T 888.594.7726		
91.2008 F 800.638.9517		
St , I 21		