
## Colectores de retorno TruFLOW Jr. con válvulas de aislamiento




Project information	
Job name:	Location:
Engineer:	Fecha de envío:
Contractor:	Presentada por:
Manufacturer's representative:	Approved by:

## Product information and application use

Use the TruFLOWTM Jr. Manifold with Isolation Valves with either the TruFLOW Jr. Manifold with Balancing Valves or the TruFLOW Jr. Valveless Manifold to complete the manifold set. The TruFLOW Jr. Manifold with Isolation Valves allows quick isolation of the loop by turning the black cap on the top of the manifold. For multiple zoning on the manifold, remove the black caps and replace with Uponor Thermal Actuators or Motorized Valve Actuators (MVAs). TruFLOW Manifold Actuator Adapters are included for mounting Thermal Actuators or MVAs. Manifolds are available in 2-, 3- and 4-loop configurations. The manifold body ends have R32 unions and the loop outlets have R20 male threads.





Installation Related applications

Manifold is shipped with the appropriate number of actuator adapters (A2630028). Refer to the TruFLOW Jr. Manifold Instruction Sheet or the Uponor Complete Design Assistance Manual for additional information.

Radiant Heating and Cooling Systems
Permafrost Prevention Systems

Turf Conditioning Systems

Footnotes	Contact information	
	Uponor Inc.	Uponor Ltd.
	5925 148th Street West	6510 Kennedy Road
•	Apple Valley, MN 55124	Mississauga, ON L5T 2X4
	T 800.321.4739	T 888.594.7726
	F 952.891.2008	F 800.638.9517