

Rouleaux rouges Uponor AquaPEX

Renseignements sur le projet

|                             |                     |
|-----------------------------|---------------------|
| Nom du poste :              | Lieu :              |
| Ingénieur :                 | Date de soumission: |
| Entrepreneur :              | Présentée par:      |
| Représentant du fabricant : | Approuvé par :      |

Données techniques

|                       |                                     |
|-----------------------|-------------------------------------|
| Material              | PEX                                 |
| Temp/pressure ratings | 73 °F (23 °C) at 160 psi (11 bar)   |
|                       | 180 °F (82 °C) at 100 psi (6.9 bar) |
|                       | 200 °F (93 °C) at 80 psi (5.5 bar)  |

Informations sur le produit et utilisation de l'application

Uponor AquaPEX® red tubing is an Engel-method, PEX-a pipe designed for hot potable-water distribution, but can also be used in radiant heating and cooling systems containing no ferrous corrodible components or where ferrous components are isolated from the tubing.

Note: Temperature and pressure ratings stated are hydrostatic ratings. For domestic hot-water (DHW) and DHW recirculation installations, operating conditions should not exceed 140°F (60°C) at 80 psi (5.5 bar) in accordance with ASTM F2023. For additional information regarding application-specific temperature and pressure ratings, refer to the Uponor PEX Piping Systems Design and Installation Manual.



| Nom de la pièce                | Numéro de pièce | Les codes                                                     | Normes                                                                                                                         | Annonces                                                                                 |
|--------------------------------|-----------------|---------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|
| Rouleaux rouges Uponor AquaPEX | All             | IMC UPC IBC IRC NBC of Canada IPC UFGS NPC of Canada UMC NSPC | ASTM F1960 ASTM E119/UL 263 ASTM F876 ASTM E84 ASTM F2023 ASTM E814/ULC S115 ASTM F877 CSA B137.5 ULC S102.2 CSA B214 ULC S101 | IAPMO-ES ICC-ES-PMG cNSFus-pw CCMC PPI TR-4 CSA UL U.P.Code cQAlus P321 HUD MR 1269 BMEC |

| L'installation                                                                                                                                                                                               | Applications connexes  |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|
| Approved fitting system is ProPEX®1. Refer to the Uponor ProPEX Connections Instructional Guide, the Uponor Professional Plumbing Installation Guide or the Uponor Piping Pocket Guide for more information. | PEX-a Plumbing Systems |

| Notes de bas de page | Coordonnées de la personne-ressource                                                                                                                                                                                              |
|----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| -                    | <div>Uponor Inc.<br/>5925 148th Street West<br/>Apple Valley, MN 55124<br/>T 800.321.4739<br/>F 952.891.2008</div> <div>Uponor Ltd.<br/>6510 Kennedy Road<br/>Mississauga, ON L5T 2X4<br/>T 888.594.7726<br/>F 800.638.9517</div> |